


Recommended Cameras for the “DELTA 20”  
using HEINE SLR Photo Adaptor

Manufacturer	Type	HEINE SLR Photo Adaptor
Canon	EOS 7D / 50D	K-000.34.185
	EOS 350 D*/400 D*	
	EOS 450 D/500 D	
	EOS 550 D / 1000 D	
Nikon	D 40*/ D 80*	K-000.34.186
	D 40X	
	D 60 / D 90	
	D 200 / D 300 S	
	D 700 / D 7000	
	D 3000 / D 5000	
Olympus	E-450 / E-510	K-000.34.187
	E-520 / E-620	

\* no longer available





## Camera setup for SLR-Adaptor

### Nikon

- ISO: 400
- Program: M
- Exposure: 1/40s
- White balance: manual

### Canon

- ISO: 400
- Program: Tv
- Exposure: 1/40s
- White balance: manual

### Olympus

- ISO: 400
- Program: S
- Exposure: 1/40s
- White balance: manual

**Canon Camera Name Chart**

<b>Europe</b>	<b>USA</b>	<b>Japan</b>	<b>MPixel</b>
Canon EOS 300D	Digital Rebel	Kiss Digital	6
350D	Rebel XT	Kiss N	8
1000D	Rebel XS	Kiss F	10
400D	Rebel XTi	Kiss X	10
450D	Rebel XSi	Kiss X2	12
500D	Rebel T1i	Kiss X3	15
550D	Rebel T2i	Kiss X4	18